



XS II

Model XS II-5K

The XStream II 5K is a rugged camera designed for flexibility in streaming environments. The Model 5K supports 5120x2880 resolution up to 400 fps and comes standard with a motorized Micro Four Thirds lens mount. With its dual-mode USB-C and XStreamLink fiber capability, XStream II camera heads integrate seamlessly with IDT's XStream Thunderbolt 3 Processor in USB-C mode or with IDT's XStream Time Servers in XStreamLink mode. Experience LIVE with INSTANT REPLAY with IDT's intuitive XStream Motion Monitor software.

- 5K Resolution
- High Speed Streaming
- Dual-Mode USB-C or Fiber Interface
- LIVE with INSTANT REPLAY

APPLICATIONS

Aerospace, Automotive, Research

KEY FEATURES

Maximum Resolution	5120 x 2880
Maximum FPS @ Maximum Res	400 fps
Operating Temperature	-40+50°C / -40+122°F

FRAME PROPERTIES

Sensor Type	CMOS - Proprietary
Sensor Size	18.4 x 10.4 mm
Sensor Format	1.3 inch
Pixel Size (micron)	3.6 x 3.6 um
Pixel Depth	12 bit mono 36 bit color
Sensitivity	6000 ISO Mono 2000 ISO Color
Min. Exposure Time	1µs (*Shorter Integration optional)
Array	8 megapixel
Quantum Efficiency	60%

MECHANICAL

Weight	.67 kg or 1.48 lbs
Dimensions	68.7 x 2.53 x 5.26 mm (W x H x L)
Mount	Motorized MFT (Standard)

TRIGGERING AND SYNCHRONIZATION

Sync In	Phase-lock TTL, IEEE
Sync Out	Frame sync / Strobe
Trigger	TTL & Switch/Circular buffer with on-camera or software trigger



POWER

Input Voltage	12VDC
---------------	-------

COMMUNICATION INTERFACE

Copper	XStreamLink USB-C
Fiber Optic	XStreamLink Fiber

EMBEDDED LOGIC

Debayering	Color Cameras Only
Temporal Noise Reduction	Standard
Dynamic Noise Reduction	Standard
User defined ROI's and LUT's	Standard
Frame to frame Auto-Exposure and Motion Trigger	Standard
Mission Mode for Remote/Autonomous Operation	Standard

SOFTWARE

XStream Motion Monitor	Windows 64
Motion Studio	Windows 32/64
Motion Inspector	Windows 32/64 - MAC OS X - Apple iOS
Plug-ins/SDK	SDK, LabVIEW™ or MatLab®
File Formats	Proprietary RAW
On-the-fly Conversion	TIF, BMP, JPG, PNG, AVI, MPG, TP2, MOV, MRF, MCF